

### KEY FEATURES


- > Low voltage piezo ceramic
- > Optimal preload for high dynamics
- > Mechanical Amplification
- > Compact Size
- > High Resolution

### RELATED PRODUCTS

- > CTEC benchtop controllers
- > CTEC OEM controllers

### AVAILABLE OPTIONS

- > Vacuum compatibility
- > Non magnetic shell



NON CONTRACTUAL PICTURE

PARAMETER	VALUE	UNIT
<b>&gt; Quasistatic performances</b>		
Nominal Stroke	34	µm
Min stroke	31	µm
Resolution <sup>(1)</sup>	1.9	nm
Blocked force	3.7	N
Stiffness	0.11	N/µm
<b>&gt; Dynamic performances</b>		
Resonance frequency (free-free) <sup>(2)</sup>	25000	Hz
Resonance frequency (blocked-free) <sup>(3)</sup>	4 800	Hz
Force limit <sup>(4)</sup>	7.5	N
<b>&gt; Control &amp; driving</b>		
Voltage range	-20 ... 150	V
Capacitance <sup>(5)</sup>	0.043	µF
<b>&gt; Dimensions &amp; interfaces</b>		
Height	4	mm
Length	9	mm
Width incl wires	5	mm
Mass	0.15	g
<b>&gt; Standard mechanical interfaces</b>	See ICD	
<b>&gt; Electrical interface</b>	See ICD	

### ANNOTATIONS


(1) Quasistatic excitation. With standard LA75 range amplifier. SNR=85 dB computed as RMS output signal /RMS output Noise float at [0;200 Hz]

(2) Free-free: The actuator mounts are free

(3) Blocked-free: The actuator is fixed to a mechanical support assumed infinitely stiff

(4) Maximum pulling or pushing external force, valid up to 90% of the blocked-free resonance frequency of the actuator

- > §§ (5) Capacitance +/- 20%, at 1 V RMS, low frequency, without load



Norme / Matière / Traitement / Ref. <b>CEDRAT TECHNOLOGIES</b> 59 Chemin du Vieux Chêne 38246 MEYLAN Cedex FRANCE TEL: 33(0)4 56 58 04 00		Niveau (9): Ce document est la propriété de Cedrat TECHNOLOGIES. Il est strictement confidentiel et ne peut être reproduit, copié ou diffusé sans l'autorisation écrite préalable de Cedrat TECHNOLOGIES. This document is the property of Cedrat TECHNOLOGIES. It is strictly confidential and cannot be reproduced, copied or disseminated without the prior written consent of Cedrat TECHNOLOGIES.	
Tolérances générales selon : General tolerances according to : Echantillonnage / Deburring : Rayon raccord / Radius curvature : Autor. / Drawn / Confidentialité / Confidentiality : OKR / Public		Révision / Revision : Etat du document / Life cycle : Edition / State : 151 Format / Page : A3 / 1/1	
Référence / Reference : <b>ICD APA30uXS NM H</b>		Révision / Revision : <b>002550-ICD-01 C</b> Applicable	